Pressure transmitter For sanitary applications Model SA-11

WIKA data sheet PE 81.80



Applications

- For gases, compressed air, vapour, liquids, pastes and powdery media
- Ultra-pure steam systems for SIP
- Hydrostatic level measurement:
- Vacuum pressure monitoring, e.g. vacuum conveyors, pump monitoring
- Food and beverage manufacturing, pharmaceutical industry, biotechnology, sanitary applications

Special features

- Wide variety of aseptic process connections, for process temperatures up to 150 °C
- Flush diaphragm with a surface roughness of Ra < 0.38 µm
- Fully welded
- Suitable for SIP and CIP
- Ingress protection up to IP 68

Description

The pressure transmitter SA-11 is designed especially for the requirements of the food and beverage, pharmaceutical and biotechnology industries.

It is particularly suitable for the special conditions of CIP/ SIP cleaning processes, such as chemical stability towards cleaning liquids and high temperatures.

The flush diaphragm is directly welded to the process connection. This guarantees a crevice-free connection of the process connection and the measuring cell so that additional sealings are not required.

For dead-space free instrumentation, aseptic process connections (clamp, threaded, VARIVENT[®] and NEUMO[®]) are available.

The SA-11 pressure transmitter is ideally suited to fulfil the stringent demands of sanitary applications and is EHEDG certified. Furthermore, the SA-11 is marked with the 3-A symbol and current version number, as it conforms, based on a third party verification, to the 3-A standard.

Design

A diaphragm made of 1.4435 stainless steel forms a flush separation of the process medium from the pressure measuring instrument.

The process pressure is transmitted hydrostatically from the diaphragm, via an FDA-approved system fill fluid, to a piezo-resistive sensor.

The measuring range covers $0 \dots 250$ mbar up to $0 \dots 25$ bar. The SA-11 pressure transmitter is powered with a DC voltage of 10 (14) ... 30 V. Available electronic output signals are $4 \dots 20$ mA, $0 \dots 20$ mA or $0 \dots 10$ V output.

A stainless steel case with an ingress protection of up to IP 68 offers a secure protection for external cleaning with splashed water and enables its use in high-humidity environments. Through the integrated cooling section, process temperatures of up to 150 °C can be realised.

WIKA data sheet PE 81.80 · 08/2014

Data sheets showing similar products: Electronic pressure switch; model PSA-31; see data sheet PE 81.85



Page 1 of 8


Pressure transmitter model SA-11 with field case and VARIVENT[®] connection

Specifications		Mod	el SA·	-11								
Measuring range	bar	0.25	0.4	0.6	1		2.5	4	6	10	16	25
Overpressure limit 1)	bar	2	2	4	5		10	17	35	35	80	80
Burst pressure	bar	2.4	2.4	4.8	6		12	20.5	42	42	96	96
	{Vacuum, ov	erpressur	e, +/-, ar	nd absolut	e pres	sure	e (from 1	bar) ar	e availab	le}		
	1) The pressure											
Process connection		see pa	ge 4 ff.									
Material												
wetted parts		Stainle	ss steel	1.4435								
■ Case		Stainless steel 1.4571										
Pressure transmission medium		Synthe	Synthetic oil, KN 77, FDA conform, FDA CFR No. 21CFR178.3750									
		{Neobe	e ® M-2	20, KN 59,	FDA o	confo	orm, FD	A CFR I	No. 21CF	R174.5	-	
Power supply U+	U+ in DC V	10 < U	+ ≤ 30 (1	14 30 fo	r 0 [.]	10 V	output s	signal, 1	1 30 V	for field	case)	
Output signal and	R_A in Ohm	4 20	mA, 2-v	vire R	A≤(U	+ - 1	0 V) / 0.	02 A				
Permissible max. load R _A		0 20	mA, 3-v	vire R	A ≤ (U	+ - 3	V) / 0.0	2 A				
		$\{0 \dots 10 \text{ V}, 3\text{-wire}\}$ R _A > 10 k {other output signals, e.g. CANopen, on requ					uest}					
Adjustability of zero point/span	%	±5 through potentiometer within the instrument										
Response time (10 90 %)	ms	≤ 10 ms										
Dielectric strength	DC V	500 ²⁾										
	2) NEC class 02	voltage supply (low voltage and low current max. 100 VA even under fault conditions)										
Accuracy ³⁾	% of span	≤ 0.5 {0.25} (Calibrated in vertical mounting position, process connection downwards)										
	3) Including non-	linearity, hysteresis, zero offset and end value deviation (corresponds to measured error per IEC 61298-2)										
Non-linearity	% of span	span ≤ 0.2 (BFSL) per IEC 61298-2										
Non-repeatability	% of span	≤ 0.1										
Stability per year	% of span	≤ 0.2	(at re	eference c	onditio	ons)						
Permissible temperature ranges												
Medium ⁴⁾	°C	-20 +	+150									
Ambient ⁴⁾	°C	-20 +	⊦80									
Storage 4)	°C	-40 +	⊦100									
	4) Also meets El	N 50178, tab.	7, operatio	on (C) 4K4H, s	storage	(D) 1K	(4, transpo	rt (E) 2K3				
Compensated temperature range	°C	0 +8	0									
Temperature coefficients in												
compensated temperature range												
Mean TC of zero point	% of span	\leq 0.2 / 10 K for measuring range 0 0.6 bar to 0 25 bar										
	% of span	an ≤ 0.25 / 10 K for measuring range 0 0.4 bar										
	% of span	≤ 0.4 /	10 K	for meas	suring	rang	ge 0 0	.25 bar				
Mean TC of span	% of span	≤ 0.2 /	10 K									
Shock resistance	g	500 pe	r IEC 60	068-2-27		(me	chanica	l shock)				
Vibration resistance	g	15 per	IEC 600	68-2-6		(vibr	ration ur	nder res	onance)			
Electrical connection		see pa	ge 4									
Wiring protection												
Overvoltage protection	DC V	36										
Short-circuit resistance		S+ vs.	U-									
Reverse polarity protection		U+ vs.	U-									
Ingress protection		In acco	ordance	with EN 6	0529/	IEC	60529,	see pa	ge 4			
Weight	kg	Approx	. 0.5 (an	prox. 0.6	with o	otion	n of linea	r error (0.25 % of	f span)		

 $\{\,\}$ $\;$ Items in curved brackets are optional extras for an additional price.

Installation example

Pressure transmitter model SA-11 with M12 x 1 circular connector and DIN 11864-1 grooved union nut mounted on a welding socket



Pressure transmitter model SA-11 and the 4 electrical connection variants



Dimensions in mm


Ingress protection IP per IEC 60529. The stated ingress protections only apply when connected and when using mating connectors that have the appropriate ingress protection.

÷

02 191. 21361 Ŧ

Electrical connections

DIN 175301-803 A Angular connector Conductor cross-section up to max. 1.5 mm², Conductor outer diameter 6-8 mm IP 65 Order code: A4



Stainless steel field case IP 67 Compression fitting, nickelplated copper alloy Order code: FH Option: field case with conduit connection

max. 90

24

55

Ø27

M12 x 1 Circular connector 4-pin IP 67 Order code: M4

Mating connectors are not included in the delivery

> M12x1 Ø? 8 2388257.




Version	Dimension H in mm					
	with accuracy 0.5 %	with accuracy 0.25 %				
Angular connector	64	84				
Field case	123	138.5				
M12 x 1	64	84				
Cable outlet	79.5	95				

Т

Other electrical connections on request

Process connections



Version		Dimen ØD	sions in mm Ød
Tri-Clamp 1)	1 1/2"	50.5	43.5
	2"	64	56.6
DIN 32676	DN 32	50.5	43.5
	DN 40	50.5	43.5
	DN 50	64	56.6
ISO 2852	DN 33.7	50.5	43.5
	DN 38	50.5	43.5
	DN 40	64	56.6
	DN 51	64	56.6



EHEDG compliant only in combination with a Kalrez stainless steel gasket from Dupont de Nemours or with a T-ring seal from Combifit International B.V.

Т

Order code: EM

Cable outlet

without access to zero point


and span potentiometer, for


end splices, conductor outer

conductor cross-sections

of 0.5 mm², AWG 20 with


diameter 6.8 mm, IP 68





Grooved union nut Ø(7	
	<u>3</u> 11490251.01

Grooved union nut APV-RJT	Ø(1		F
			11490293.01
			-
		2.6	
	Ø(12		
	Ø(7	-	
-	G	-	



Version		Dimensions in mm			
		G	Ød ₃		
DIN 11851	DN 25	Rd 52 x 1/6	44		
	DN 40	Rd 65 x 1/6	48		
	DN 50	Rd 78 x 1/6	61		



3-A compliant only in combination with profile sealing from SKS Komponenten BV or Kieselmann GmbH.

EHEDG compliant only in combination with ASEPTO-STAR k-flex upgrade sealing from Kieselmann GmbH $% \left({{\rm S}_{\rm A}} \right)$

Version		Dimensions in mm			
		G	Ød ₃		
SMS	1 1/2"	Rd 60 x 1/6	47.5		
	2"	Rd 70 x 1/6	60		

Version		Dimen	sions i	in mm
		G	ØC ₂	ØC7
IDF	1 1/2"	IDF 1.5	42.5	47
	2"	IDF 2	56	60.5

 $3\mbox{-}A$ compliant only in combination with a sealing with support ring per ISO 2853

Version		Dimensio	Dimensions in mm					
		G	ØC1	ØC7	ØC ₁₂			
APV-RJT	1 1/2"	2 5/16" x 8	45.2	54	40.5			
	2"	2 7/8" x 6	57.7	66.6	53.2			

VARIVENT® Form F 50	Version		Dimensions in mm ØD	
	VARIVENT®	Form F	50	
Form N 68		Form N	68	


EHEDG compliant only in combination with EPDM O-ring




CERTIFIED

EHEDG

Grooved union nut



Flage connection DIN 11864-2 Fla




11490544.01

11490668.01

11490668.01

Clamp connection DIN 11864-3



Version Dimensions in mm G DIN 11864-1 DN 40 Rd 65 x 1/6 54.9 DN 50 Rd 78 x 1/6 66.9



Version		Dime	nsions	in mm		
						Øb ₂
DIN 11864-2	DN 40	65	82	53.7	4 x 9	10
	DN 50	77	94	65.7	4 x 9	10
				5	ر ® ۲	ERTIFIED
				//	7/ 🐧	Sector Sector
					3\\	EHEDG

Version		Dimens Ød ₁₀	ions in mm Ød ₁₁
DIN 11864-3	DN 40	64	53.7
	DN 50	77.5	65.7



Arean analy a


Version		Dimensions in mm						
		Ød		ØD	Øk	h	Н	
BioControl ®	Size 50	50	4x9	90	70	17	27	
	Size 65	68	4x11	120	95	17	27	

suitable for mounting to a NEUMO ${\rm BioControl}^{\circledast}$ case, see data sheet AC 09.14




	Dimensions in mm					
		Ød ₂	Ød4	ØD	Øk	FB
BioConnect ®	DN 40	4 x 9	44.2	100	80	10
	DN 50	4 x 9	56.2	110	90	12

NEUMO **BioControl**®




NEUMO



NEUMO

BioConnect® Collar connecting sleeve for threaded connection (form V)




Version		Dimensions in mm				
		G	Ød4	ØD		
BioConnect®	DN 40	M56 x 2	44.2	53		
	DN 50	M68 x 2	56.2	65		



3-A compliant in self-draining mounting position (see data sheet DS 99.39, bottom of page 2)





Other process connections on request

Electrical connections

Version	2-wire	3-wire
Angular connector DIN 175301-803 A		
Stainless steel field case	U+ 12345	
Circular connector M12 x 1, 4-pin		
Cable outlet with 1.5 m cable length	U+ brown	U+ brown
Legend: Voltage supply Load	(2) green	S+ (3) white U- green

11489520.01

CE conformity

EMC directive

2004/108/EC, EN 61326 emission (group 1, class B) and interference immunity (industrial application)

RoHS conformity

Yes

Approvals

- GOST, metrology/measurement technology, Russia
- **GOST-R**, import certificate, Russia
- **CRN**, safety (e.g. electr. safety, overpressure, ...), Canada
- **CSA**, safety, sanitary applications, Canada

Certificates 1)

- 2.2 test report per EN 10204 (e.g. state-of-the-art manufacturing, material proof, indication accuracy for diaphragm seal systems)
- 3.1 inspection certificate per EN 10204 (e.g. material proof for wetted metallic parts, indication accuracy for diaphragm seal systems)
- FDA conformity of the system fill fluid
- 3-A conformity only in connection with the abovementioned process connections, based on third party verification, in accordance with 3-A standard No. 74
- EHEDG conformity only in connection with the process connections appropriately marked above
- Manufacturer's declaration regarding EU regulation 1935/2004 EC
- Others on request

1) Option

Approvals and certificates, see website

Ordering information

Model / Output signal / Measuring range / Process connection / Electrical connection / Certificates / Options

© 2005 WIKA Alexander Wiegand SE & Co. KG, all rights reserved. The specifications given in this document represent the state of engineering at the time of publishing. We reserve the right to make modifications to the specifications and materials.

Page 8 of 8

WIKA data sheet PE 81.80 · 08/2014



WIKA Alexander Wiegand SE & Co. KG Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Tel. +49 9372 132-0 Fax +49 9372 132-406 info@wika.de www.wika.de